Index Plungers • with mounting flange, horizontal, stainless steel 22110.2345



Product Description

Index plungers are used for indexing bores.

Material

Housing

 Stainless steel 1.4308, precision casting, bright, matt blasted

Locking pin

Stainless steel 1.4305

Knob

• Thermoplastic PA 6, black, dull

Assembly

Assembly by means of washers ISO 7092.

Operation


When using locking index plungers, the knob is pulled-out, turned 90° and secured by a notched catch (when locking pin should not overhang).

More information

Notes

Knob not removable.

Drawing



Order information

	Dimensions														oring ad ¹⁾	B		I	Art. No.
d ₁		b ₁	b ₂	b ₃	b ₄ -0.2	h ₁	h ₂	k ₁ ±0.05	k ₂	k ₃	k ₄	l ₁	l ₂ min.	F ₁	F ₂ ~	min.	max.		
	[mm]													[N]		[°C]		[g]	
wit	with knob and locking – picture 3																		
5	16	25.5	28	8	4.3	4.5	9.5	18	5	10	10.5	43.5	5	5	24	-30	80	30	22110.2345

¹⁾ statistical average value

www.halder.com Page 1 of 2
Published on: 10.8.2024

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals



Erwin Halder KG

www.halder.com Page 2 of 2 Published on: 10.8.2024