

绞链 · 长
25165.0265



产品描述

The different versions cover many applications that require a low load. These metal hinges are characterised by their simple design and the different versions:



- without bores
- with bores
- with bores for countersunk screws

The version without bores can be assembled by welding or by inserting a specific drilling pattern.

材质

- 本体
- 不锈钢 1.4301
- 轴
- 不锈钢 1.4301

图面



订单信息

尺寸										夹持力			品号
b ₁	l ₁	b ₂	d ₁	d ₂	d ₃	h ₁ ~	h ₂	l ₂	F ₁ ~	F ₂ ~	F ₃ ~	[g]	
[mm]										[N]			
with bores for countersunk screws – 相片 3, 不锈钢													
60	90	36	5	6	8,3	10	2	33	3000	3000	1200	121	25165.0265

遵守

符合 RoHS

符合指令 2011/65/EU 和指令 2015/863

不含 SVHC 物质

不含超过 0.1% w/w 的 SVHC 物质 - 截至 2024 年 1 月 23 日的 SVHC 清单.

不含 65 号提案物质

不包括 65 号提案物质

<https://www.P65Warnings.ca.gov/>

不含冲突矿物

„本产品不含来自刚果民主共和国或邻近国家的任何被指定为“冲突矿物”的物质，例如钽、锡、金或钨。