

Panty

25165.0040



Popis produktu

The different versions cover many applications that require a low load.

These metal hinges are characterised by their simple design and the different versions:

- without bores
- with bores
- with bores for countersunk screws

The version without bores can be assembled by welding or by inserting a specific drilling pattern.

Materiál


Základní těleso

- Nerez 1.4301

Osa

- Nerez 1.4301


Výkres s rozměry



picture 1

picture 2

picture 3



Informace pro objednání

b ₁	l ₁	Rozměry			F ₁	Přidrzná síla			Obj. č.	
		d ₂	h ₁	h ₂		F ₂	F ₃	[g]		
without bores – obrázek 1, Nerez										
50	50	6	10	2	2500	2000	1000	62	25165.0040	

Shoda

Vyhovuje RoHS

V souladu se směrnicí 2011/65/EU a směrnicí 2015/863.

Neobsahuje látky SVHC

Žádné látky SVHC s obsahem vyšším než 0,1% hm. - seznam SVHC k 23.01.2024.

Neobsahuje látky Proposition 65

Neobsahuje látky Proposition 65.

<https://www.P65Warnings.ca.gov/>

Bez konfliktních minerálů

Tento produkt neobsahuje žádné látky označené jako "konfliktní minerály" jako je tantal, cín, zlato nebo wolfram z Demokratické republiky Kongo nebo sousedních zemí.