

## Locating Bushings · for ball lock pins and socket pins

22400.0926



### Product Description

This design with holes on the front face (picture 2) is suitable for applications which require installation flush to the surface.

Locating bushings are used for quick and safe locating of ball lock pins EH 22340., EH 22350., EH 22370. and EH 22380. and socket pins EH 22400.

Optimised centering due to precise collar (e.g. quick mounting of plates and components). All versions are corrosion and abrasion resistant.

### Material


- Stainless steel 1.4305

### Assembly

This design with holes on the front face (picture 2) can be installed via a cranked pin face wrench or alternatively via a pin faced socket wrench.

Ensure safe tolerances and consistent function. Easily incorporable into different materials. Can be used in thin-walled pieces. Application from both sides.



### Drawing




### Order information

| Dimensions                        |                |                |                |                |                |                |                |                |                |                |                |     | [g]        | Art. No. |  |
|-----------------------------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|-----|------------|----------|--|
| d <sub>1</sub>                    | d <sub>2</sub> | d <sub>3</sub> | d <sub>4</sub> | d <sub>5</sub> | l <sub>1</sub> | l <sub>2</sub> | l <sub>3</sub> | l <sub>4</sub> | l <sub>5</sub> | l <sub>6</sub> | l <sub>7</sub> |     |            |          |  |
| H11                               |                | h9             |                | +0.1           |                |                |                |                |                |                |                |     |            |          |  |
| [mm]                              |                |                |                |                |                |                |                |                |                |                |                |     |            |          |  |
| plain, with face hole – picture 2 |                |                |                |                |                |                |                |                |                |                |                |     |            |          |  |
| 20                                | M36            | 43             | 25.5           | 5.1            | 49             | 42             | 17.5           | 31.5           | 11.9           | 23.1           | 30             | 364 | 22400.0926 |          |  |

### Accessories

|   | Suitable for size<br>d <sub>1</sub><br>[mm] | For finish<br>picture | Pin spacing<br>±0.1<br>[mm] | Pin diameter<br>-0.1<br>[mm] | Square drive<br>[in] | [g] | Art. No.   |
|---|---|-----------------------|-----------------------------|------------------------------|----------------------|-----|------------|
| adjustable face wrench, offset  |   |                       |                             |                              |                      |     |            |
|  | 10/12/16/20/25                              | 2                     | –                           | 5                            |                      | 309 | 22350.1991 |
| face wrench (socket wrench insert)  |   |                       |                             |                              |                      |     |            |
|  | 16/20                                       | 2                     | 30                          | 5                            | 1/2                  | 243 | 22350.1998 |

### Application example



### Compliance

#### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

#### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

#### Does not contain Proposition 65 substances

No Proposition 65 substances included.  
<https://www.P65Warnings.ca.gov/>

#### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.