Mounting Pads • protected against slipping

22590.1010



Product Description

Mounting pads can be used as foot or thrust pad. Not parallel bearing surfaces up to 15° degrees can be compensated.

The plastic cover on the mounting pad prevents slipping.

Ball element

• Free cutting steel, induction-hardened, blackened.

Rubber cap

· Rubber, black


Pad

· Heat-treated steel, tempered, blackened


More information

For the versions d_1 = M10 and M12 the lock nut conforms to DIN 934.

Drawing



picture 1



picture 2

Order information

d ₁	$\begin{array}{c ccccccccccccccccccccccccccccccccccc$				ws	Load capacity for static load	Ĭ	Art. No.
		~ [mm]			[mm]	max. [kN]	[9]	
pad and ball element – picture 1, Heat-treated steel								
M10	36	26	11	9	17	20	80	22590.1010

Erwin Halder KG

www.halder.com Page 1 of 2 Published on: 10.8.2024

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Erwin Halder KG

www.halder.com Page 2 of 2

Published on: 10.8.2024