Positioning Clamping Pins 23111.0027



Product Description

The positioning clamping pin allows fast clamping, fastening, adjusting, changing and securing of workpieces, plates, fixture systems etc.

Material

• Heat-treated steel, tempered, blackened

Operation

By tightening the clamping bolt, the positioning clamping pin is centred and clamped in the locating bushing by means of four balls. The clamping bolt can be operated manually via a removable handle (Art. No. 23111.0900/.0902) or using a hexagon key.

More information

Accessories


Suitable bushings are available.


Further products

- Manual Handles, for positioning clamping pins
- Bushings, for positioning clamping pins
- Locating Bushings, for positioning clamping pins, for press fit
- Locating Bushings, for positioning clamping pins, for screw fit

CE

Drawing







Order information

Dimensions								For base	WS₁	WS ₂	Holding force	Ť.	Art. No.
d ₁ -0.02 -0.05	Ι ₁ +0.6	d ₂	d ₃	d₄	Ι ₂ ±1	I ₃	s max.	plates ±0.05				-	
[mm]								[mm]	[mm]	[mm]	[kN]	[g]	
Heat-trea	ted steel												
25	30	29	45	M4	18.6	10	11	25	43	10	8	287	23111.0027

Application example





Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances

Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.

