Clamps ⋅ slotted, with adjustable counter piece, with T-bolt 23185.0117



Product Description

The thrust pad and the counter element are connected with the clamp and therefore secured against loss. Consequently, the clamp is quickly ready for use. The clamp is equipped with two flat noses and can be turned around depending on the case of application.

Material

Screw

· Heat-treated steel

Nut

· Heat-treated steel

Disc

· Heat-treated steel

Clamp

 Steel, tempered, zinc-plated by galvanization

More information


References

Larger clamping heights can be reached by the use of a support extension (EH 23185.).

Further products

• Support Extensions, for straight clamps, slotted, with adjustable counter piece

Drawing



Erwin Halder KG

Order information

Nomina	T-	Dimensions															ws	Clamping	I	Art. No.
dimensio	slot	d ₂	l ₄	h ₁	h ₂	a ₁	a ₂	a ₃	b ₁	b ₂	I ₁	l ₂	l ₃	е	С	s		force ¹⁾	_	
d ₁	size																	max.		
[mm]	[mm]		[mm]															[kN]	[g]	
17	18	M16	160	0 – 70	20	36	17	21	55	41	150	35	36	25	17.6	12	24	40	1895	23185.0117

¹⁾ stated clamping forces in optimal clamping position (smallest distance of the socket head screw to the clamping position). Clamping forces can vary depending on clamping, strength class of the socket head screw and condition of the thread (lubrication).

www.halder.com Page 1 of 2

Published on: 10.8.2024

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 2 of 2
Published on: 10.8.2024

Erwin Halder KG