# Eccentric Quick Clamps • with screw 23390.0309



# **Product Description**

For quick and easy clamping and releasing of workpieces. When using the "adjustable" design (picture 2) the lever position can be moved.

#### Material

# Support washer

Thermoplastic POM, glass-fiber reinforced

· Zinc die-cast, plastic coated, black, similar to RAL 9005

## Inner parts

• Stainless steel 1.4305


#### Screw


• Stainless steel 1.4305

#### Adjusting nut

• Stainless steel 1.4305

### **Drawing**





### **Order information**

Dimensions								Stroke		I	Art. No.
I	d <sub>2</sub>	h <sub>1</sub> max. in clamping position	d <sub>3</sub>	d₄	h <sub>2</sub> max.	Regulating- range h <sub>3</sub> min.	b	s at 90° lever position	max.		
[mm]								[mm]	[°C]	[g]	
with screw, adjustable – picture 2, Stainless steel											
63	М6	16	16	19	16.4	1.5	16	0.75	80	69	23390.0309




Erwin Halder KG

www.halder.com Page 1 of 2

Published on: 10.8.2024

# **Application example**



# Compliance

# **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

#### **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 2 of 2 Published on: 10.8.2024