Adjustable Clamping Levers • with screw

24400.0263



Product Description

Adjustable clamping levers find versatile applications when the area of use is confined or a specific lever position is required.

Material

Lever

 Zinc die-cast, plastic coated, silver, similar to RAL 9006, matt structure

Inner parts

• Steel, blackened, quality 5.8

Screw

• Steel, blackened, quality 5.8

Operation


By lifting the lever the serrations are disengaged. The lever can be positioned by the serrations. On releasing the lever, the serrations are automatically re-engaged.

More information

Notes

The screw part can be exchanged.

Drawing




Order information

Dimensions									I	Art. No.
d ₁	d ₂	I ₁	d ₃	h ₁	h ₂	h ₃	h ₄	l ₂		
[mm]									[g]	
silver										
18	M6	40	13.5	31	6.5	3	45	62	76	24400.0263



www.halder.com Page 1 of 2
Published on: 10.8.2024

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 2 of 2 Published on: 10.8.2024

Erwin Halder KG