# Adjustable Clamping Levers • with screw 24400.0661



#### **Product Description**

Adjustable clamping levers find versatile applications when the area of use is confined or a specific lever position is required.

#### **Material**

#### Lever

• Zinc die-cast, plastic coated, orange similar to RAL 2004, matt structure

#### Inner parts

Steel, blackened, quality 5.8

# Screw

• Steel, blackened, quality 5.8

#### Operation


**By lifting the lever** the serrations are disengaged. The lever can be positioned by the serrations. On releasing the lever, the serrations are automatically re-engaged.

#### More information

#### Notes

The screw part can be exchanged.


# Drawing



#### **Order information**

	Dimensions								Ĭ	Art. No.
d <sub>1</sub>	d <sub>2</sub>	I <sub>1</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	I <sub>2</sub>	_	
				[mm]					[9]	
orange										
30	M16	50	23	50.5	12	5	76	108	370	24400.0661

# **Application example**



# Compliance

#### **RoHS compliant**

Contains lead - compliant according to exceptions 6a / 6b / 6c.

# Contains SVHC substances >0,1% w/w Contains lead - SVHC list [REACH] as of 27.06.2024.

#### **Contains Proposition 65 substances**

# 

Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

# Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.