Adjustable Tension Levers 24440.0750



Product Description

Material

Lever

Stainless steel 1.4305, dull blasted

Screw

Stainless steel 1.4305

Ball knob

Thermosetting plastic PF 31, black, DIN 319

Operation


By lifting the lever the serrations are disengaged. The lever can be positioned by the serrations. On releasing the lever, the serrations are automatically re-engaged.

More information

Notes

The threaded portion can be exchanged.

Drawing



Order information

Dimensions											Art. No.
d ₁	d ₂	l ₁	d ₃	d ₄	d₅	h1	h ₂	h ₃	1	-	
									~		
[mm]										[9]	
with screw – picture 2, Stainless steel											
28	M12	63	19	12	30	48.5	4.5	4.5	110	312	24440.0750

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances No Proposition 65 substances included.

https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.