Ball Knobs • DIN 319 24560.0225



Product Description

The DIN 319 ball knobs are jointless and polished.

Material

Bushing

Steel, zinc-plated by galvanization


Ball


 Thermosetting plastic PF 31, black similar to RAL 9005

Assembly


Assembly instruction for form M: Fitted by lightly tapping with a hammer, holds in position without being cemented. For the counter element a h9-fit is sufficient.

Drawing





picture 2




picture 3

Order information

Dimensions					For pin	<u>.</u>	ă.	Art. No.
d ₁	d ₃	d ₄ ~	h ~	t ₃ min.	h9	max.		
[mm]					[mm]	[°C]	[9]	
with taper bore	form M – pict	ure 3, black						
25	6	15	22.5	15	6	110	9.3	24560.0225

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.