Ball Knobs • DIN 319

24560.0240



Product Description

The DIN 319 ball knobs are jointless and polished.

Material

Bushing


• Steel, zinc-plated by galvanization

· Thermosetting plastic PF 31, black similar to **RAL 9005**

Assembly

Assembly instruction for form M: Fitted by lightly tapping with a hammer, holds in position without being cemented. For the counter element a h9-fit is sufficient.


Drawing



Order information

Dimensions					For pin h9	<u>D</u>	I	Art. No.
d ₁	d ₃	d₄ ~	h ~	t ₃ min.	119	max.		
[mm]					[mm]	[°C]	[9]	
with taper bore form M – picture 3, black								
40	10	22	37	20	10	110	39	24560.0240

Application example



Erwin Halder KG

Page 1 of 2 www.halder.com

Published on: 10.8.2024

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 2 of 2 Published on: 10.8.2024