High Knurled Thumb Screws • DIN 464 24790.0140



Product Description

Knurled thumb screws are very versatile. Three material versions for the different requirements • steel, blackened

- steel, zinc-plated by galvanization
- stainless steel
- are available.

Knurled thumb screws can be easily tightened and released by hand. The ribbed outer surface of the nut prevents slipping when tightening / releasing with the fingers.

Knurled screws are one-piece manufactured. Contrary to the Standard Sheet, they are generally manufactured with a thread up to the head and with runout without undercut at the end of the thread. The screws can therefore not be screwed in up to the collar.

Material

• Steel, blackened, quality 5.8

More information


Notes

Knurling pitch and knurling depth may differ from DIN.

Further products

• Flat Knurled Thumb Screws, DIN 653








Order information

Dimensions						I	Art. No.
d ₁	1	d ₂	d ₃	h	k	-	
	[mm]					[g]	
Steel							
M6	25	24	12	15	5	30	24790.0140

Application example







Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.