

Tuercas de Sujeción • soldada, bilateral

EH 24470.




Descripción del Producto

Permite la utilización con las dos manos.

Material

- Acero, cincado por galvanización
- Acero inoxidable 1.4301, mate


Dibujo



Información para el pedido

l	d ₁	Dimensiones			h ₁	h ₂	g	Referencia
		d ₂	d ₃	[mm]				
Acero								
47,5	M 8	16	10	12,5	26	63	24470.0706	
59,5	M10	20	12	15,0	32	116	24470.0708	
75,5	M12	25	14	19,0	40	210	24470.0710	
94,5	M16	32	18	25,0	52	432	24470.0712	
118,0	M20	40	20	31,0	62	716	24470.0716	
Acero inoxidable								
47,5	M 8	16	10	12,5	26	63	24470.0806	
59,5	M10	20	12	15,0	32	116	24470.0808	
75,5	M12	25	14	19,0	40	210	24470.0810	
94,5	M16	32	18	25,0	52	432	24470.0812	
118,0	M20	40	20	31,0	62	716	24470.0816	

Ejemplo de aplicación



Cumplimiento

Para obtener información detallada sobre el cumplimiento, seleccione el número de artículo deseado.