# V-Blocks 1648.100




# **Product Description**

## **Material**

• Steel, case-hardened, ground


# Drawing



# Order information

System	Dimensions								<b>I</b>	Art. No.
	I <sub>1</sub>	h <sub>1</sub>	h <sub>2</sub>	d1	d <sub>2</sub>	d <sub>3</sub>	<b>d</b> ₃ min.	<b>d</b> ₃ max.	-	
	[mm]								[g]	
L16	98	35	152	16	M16	100	18	190	1451	1648.100

## **Application example**



## Compliance

### **RoHS compliant**

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

#### Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

#### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.