Index Plungers • with mounting flange, horizontal, stainless steel 22110.2308



Product Description

Index plungers are used for indexing bores.

Material

Housing

 Stainless steel 1.4308, precision casting, bright, matt blasted

Locking pin

• Stainless steel 1.4305

Pull-ring

Stainless steel 1.4310

Assembly

Assembly by means of washers ISO 7092.

Operation


When using locking index plungers, the knob is pulled-out, turned 90° and secured by a notched catch (when locking pin should not overhang).


More information


Notes


Knob not removable.

Drawing














picture 3

Order information

	Dimensions														g load ¹⁾		I	Art. No.
d ₁		b ₁	b ₂	b ₃	b ₄ -0.2	h ₁	h ₂	k ₁ ±0.05	k ₂	k ₃	k ₄	I ₁	I ₂ min.	F ₁ ~	F ₂ ~	max.		
	[mm]														[N]	[°C]	[g]	
wit	with pull-ring, without locking – picture 1																	
	30	33	34	12	5.4	6	12.5	23	5.5	12	15.5	71	8	6	22	100	67	22110.2308

¹⁾ statistical average value

Erwin Halder KG

er.com Page 1 of 2 Published on: 10.8.2024

www.halder.com

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals



Erwin Halder KG

www.halder.com Page 2 of 2 Published on: 10.8.2024