Index Plungers • without hexagon collar 22120.0445



Product Description

Index plungers are used for indexing bores.

Material

Body

Stainless steel 1.4305

Locking pin

Stainless steel 1.4305, nickel-plated

Knob

Thermoplastic PA 6, black

Assembly

Suitable mounting tools are available.

More information


Notes

Knob not removable. Lock nuts have to be purchased separately.

Further products

- Mounting Blocks, for index bolts and index plungers, die-cast
- Locating Bushings, for index bolts and index plungers
- · Distance Collars, for index plungers

Drawing



Order information


Dimensions						Spring load ¹⁾		ß		Ĭ	Art. No.
d ₁ -0.02 -0.05	d ₂	d ₃	ι ₁ ~	l ₂ min.	I ₃	F1 ~	F ₂ ~	min.	max.		
	[mm]						[N]	[°C]]	[g]	
with knob – picture 1, Stainless steel											
5	M10 x 1	21	45	5	22	6	14	-30	80	17	22120.0445

1) statistical average value

Accessories

	Dimensions d ₂	Wrench size	Ĭ	Art. No.						
	[mm]	[mm]	[9]							
Lock nuts ISO 8675 (DIN 439), Stainless steel										
	M10 x 1	16	5.2	22120.0515						
assembly tool, Steel										
	M10 x 1	_	9.3	22120.0955						

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.