Mounting Pads 22590.0212



Product Description

Mounting pads can be used as foot or thrust pad. Not parallel bearing surfaces up to 15° degrees can be compensated.

Material

Ball elementStainless steel 1.4305

Pad


Stainless steel 1.4305


More information

Notes

For the versions $d_1 = M10$ and M12 the lock nut conforms to DIN 934.

Drawing






Order information

Dimensions d ₁ d ₂ h ₁ h ₂ t					WS	Load capacity for static load	max.	Ĭ.	Art. No.
	-	~ [mm]	_		[mm]	max. [kN]	[°C]	[9]	
pad and ball element – picture 1, Stainless steel									
M12	40	26	6	11	19	28	250	113	22590.0212

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.