# Studs • DIN 6379 b long for nuts for T-slots

# 23040.0606



# **Product Description**

Studs combined with T-nuts DIN 508 (EH 23010./23020.), fixture nuts DIN 6330 (EH 23070.) and plain washers DIN 6340 (EH 23060.) become complete clamping studs. These studs are characterised by the rolled thread.

#### Material

· Heat-treated steel

#### More information


#### References

For torques and strengths please refer to appendix - Technical Data -

# **Further products**

- Nuts for T-Slots, DIN 508
- Studs, DIN 6379 for nuts for T-slots
- Studs, with internal hexagon, similar to DIN 6379, for nuts for T-slots
- Shaft / Plain Washers, DIN 6340 heattreated
- Fixture Nuts, DIN 6330 (height 1,5 d)

# **Drawing**



#### **Order information**

Dimensions				I	Art. No.
d	I	<b>b</b> <sub>1</sub>	b <sub>2</sub>	_	
	[mm]			[9]	
quality 10.9					
M10	200	25	122	98	23040.0606


## **Application example**





www.halder.com Page 1 of 2

Published on: 16.10.2024



# Compliance

# **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

#### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

#### Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

## **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 2 of 2 Published on: 16.10.2024