

Clamps • DIN 6316 with goose-neck 23160.0035



Product Description

This clamp (clamping claw) according to DIN 6316 with goose-neck is mainly used in mechanical clamping technology for clamping workpieces.

Material

- Heat-treated steel, varnished


Drawing



Order information

Nominal dimension b_1 [mm]	Dimensions								For screws		[g]	Art. No.
	l	a	b_2	b_3	c	e_1	e_2	h	[mm]	[in]		
33	315	50	80	40	40	91	100	100	M30	1 1/4	8340	23160.0035

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.