Down-Hold Clamps • with cranked tension lever

23210.0325



Product Description

The quick-acting clamping element simultaneously presses the workpieces towards both, the stops and fixture plate. The low profile construction enables the entire surface to be machined. In conjunction with cylindrical stops EH 23280., a special fixture can be replaced.

Materia


• Steel, case-hardened, blackened


More information

Further products

· Stops, cylindrical

Drawing






Order information

T-slot	Dimensions												Clamping	I	Art. No.
size	d₁	а	b	d ₂	h ₁	h ₂	h ₃	h ₄	I ₁	l ₂	l ₃	S	force horizontal max.	_	
[mm]	[mm]													[g]	
with flat	with flat clamping jaw, clamping to the left														
12	M12	11.6	48	12.5	38	63	16	62	190	72	40	4	7	868	23210.0325

Application example





www.halder.com Page 1 of 2
Published on: 10.8.2024

Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Erwin Halder KG

www.halder.com Page 2 of 2
Published on: 10.8.2024

www.halder.com