Eccentric Quick Clamps • with female thread 23390.0103



Product Description

For quick and easy clamping and releasing of workpieces. When using the "adjustable" design (picture 2) the lever position can be moved.

Material

Support washer

· Thermoplastic POM, glass-fiber reinforced

· Zinc die-cast, plastic coated, black, similar to RAL 9005

Threaded part

· Steel, zinc-plated by galvanization


Inner parts

• Steel, zinc-plated by galvanization

Adjusting nut

• Steel, zinc-plated by galvanization

Drawing



Order information

Dimensions									Stroke		I	Art. No.	
I	d₁	d ₃	d ₄	h₂ max.	Regulating- range h ₃ min.	b	t ₁	t ₂ min. in clamping position	s at 90° lever position	max.			
[mm]									[mm]	[°C]	[g]		
with fem	with female thread, adjustable – picture 2, Steel												
63	M5	16	19	16.4	1.5	16	13	3	0.75	80	66	23390.0103	




Erwin Halder KG

www.halder.com Page 1 of 2

Published on: 10.8.2024

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Erwin Halder KG

Page 2 of 2 Published on: 10.8.2024

www.halder.com