# Eccentric Quick Clamps • with screw 23390.0109



#### **Product Description**

For quick and easy clamping and releasing of workpieces. When using the "adjustable" design (picture 2) the lever position can be moved.

#### Material

### Support washer

Thermoplastic POM, glass-fiber reinforced

#### Lever

Zinc die-cast, plastic coated, black, similar to RAL 9005

#### Inner parts

Screw


· Steel, zinc-plated by galvanization


## Steel, zinc-plated by galvanization

Adjusting nut

Steel, zinc-plated by galvanization

#### Drawing






#### **Order information**

Dimensions								Stroke	ß	Ĩ	Art. No.
I	d <sub>2</sub>	h₁ max. in clamping position	d <sub>3</sub>	d₄	h₂ max.	Regulating- range h <sub>3</sub> min.	b	s at 90° lever position	max.		
[mm]								[mm]	[°C]	[g]	
with screw, adjustable – picture 2, Steel											
63	M6	16	16	19	16.4	1.5	16	0.75	80	69	23390.0109

#### **Application example**



#### Compliance

#### **RoHS compliant**

Contains lead - compliant according to exceptions 6a / 6b / 6c.

#### Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

#### **Contains Proposition 65 substances**

Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

#### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.