Eccentric Quick Clamps • with screw 23390.0134



Product Description

For quick and easy clamping and releasing of workpieces. When using the "adjustable" design (picture 2) the lever position can be moved.

Material

Support washer

Thermoplastic POM, glass-fiber reinforced

Lever

Zinc die-cast, plastic coated, black, similar to RAL 9005

Inner parts

Screw


· Steel, zinc-plated by galvanization


Steel, zinc-plated by galvanization

Adjusting nut

Steel, zinc-plated by galvanization

Drawing






Order information

Dimensions								Stroke		Ĭ	Art. No.
I	d ₂	h₁ max. in clamping position	d ₃	d₄	h₂ max.	Regulating- range h ₃ min.	b	s at 90° lever position	max.		
[mm]								[mm]	[°C]	[g]	
with screw, adjustable – picture 2, Steel											
63	M5	35	16	19	16.4	1.5	16	0.75	80	71	23390.0134

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances

Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.