Adjustable Clamping Levers • with female thread 24400.0311



Product Description

Adjustable clamping levers find versatile applications when the area of use is confined or a specific lever position is required.

Material

Lever

• Zinc die-cast, plastic coated, orange similar to RAL 2004, matt structure

Threaded part

• Steel, blackened, quality 5

Inner parts

• Steel, blackened, quality 5.8

Operation


By lifting the lever the serrations are disengaged. The lever can be positioned by the serrations. On releasing the lever, the serrations are automatically re-engaged.

More information

Notes

The threaded portion can be exchanged.






Order information

Dimensions									I	Art. No.
d ₁	d ₂	d ₃	h ₁	h ₂	h ₃	h ₄	I ₂	t	-	
								≥		
	[mm]									
orange										

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances

Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.