Adjustable Tension Levers 24440.0134



Product Description

Material

Lever

Steel, blackened

Inner parts

Steel, blackened, quality 5.8

Screw

Steel, blackened, quality 5.8

Ball knob

• Thermosetting plastic PF 31, black, DIN 319

Operation


By lifting the lever the serrations are disengaged. The lever can be positioned by the serrations. On releasing the lever, the serrations are automatically re-engaged.

More information

Notes

The threaded portion can be exchanged.

Drawing



Order information

Dimensions										Ĩ	Art. No.
d ₁	d ₂	l ₁	d ₃	d4	d₅	h1	h ₂	h ₃	I	-	
[[g]	
with screw – picture 2, Steel											
21	M8	63	13.5	8	20	33.5	4	1	70	114	24440.0134

Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances

Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.

