# Hinges • elongated on one side 25165.0180



## **Product Description**

The different versions cover many applications that require a low load.

- These metal hinges are characterised by their simple design and the different versions:
- · without bores
- with bores
- with bores for countersunk screws
- The version without bores can be assembled by welding or by inserting a specific drilling pattern.

## Material


Body

Stainless steel 1.4301

Axis


• Stainless steel 1.4301


# Drawing











ì.

# **Order information**

Dimensions									Holding force			I	Art. No.	
b <sub>1</sub>	l <sub>1</sub>	b <sub>2</sub>	b <sub>3</sub>	d <sub>1</sub>	d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	I <sub>2</sub>	F <sub>1</sub>	F <sub>2</sub>	F <sub>3</sub>	_		
						~			~	~	~			
[mm]									[N]			[g]		
with bore	with bores – picture 2, Stainless steel													
90	60	48	18	5.2	6	10	2	36	1100	2500	1000	108	25165.0180	

#### Compliance

#### **RoHS compliant**

Compliant according to Directive 2011/65/EU and Directive 2015/863.

#### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

#### Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

#### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.