Hinges • long version 25165.2020



Product Description

The different versions cover many applications that require a low load.

- These metal hinges are characterised by their simple design and the different versions:
- · without bores
- with bores
- with bores for countersunk screws
- The version without bores can be assembled by welding or by inserting a specific drilling pattern.

Material

Body


• Steel, zinc-plated by galvanization, passivated


h₁


Axis

Stainless steel 1.4301

Drawing








မီ စြီ



picture 3



picture 2

Order information

Dimensions									F	lolding force		Art. No.	
b ₁	l ₁	b ₂	d ₁	d ₂	d ₃	h ₁	h ₂	l ₂	F ₁	F ₂	F ₃	_	
						~			~	~	~		
[mm]									[N]			[g]	
with bore	s for coun	tersunk so	rews –	picture	3, Steel								
30	45	18	4	3	6.4	6	1.5	16.5	1300	750	700	21	25165.2020

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.