

SIMPLEX sledge hammers • Rubber composition / nylon; with cast iron housing and Hickory handle

3028.081



Product Description

Available with the insert combination of rubber composition / nylon, the SIMPLEX sledge hammer of the series 3028 covers an extensive range of applications and is therefore widely used in the metal working industry.

Ultra low-wear, impact cushioning and odourless, the medium hard rubber insert (series 3202) offers a much longer service life than a conventional rubber hammer.

The nylon insert (series 3208) offers outstanding impact qualities and is guaranteed to combine maximum strength with unique durability. It is composed of extruded and extremely homogeneous material. Compared to injection moulded plastic inserts, it is therefore considerably more wear-resistant and durable and will never chip even in sub-zero temperatures. Moreover, it is also oil and grease resistant.

Made of cast iron, the housing comes with an integrated handle protection sleeve that provides for a high level of break resistance.

The long-fibre and ultra durable hickory handle is varnished and shaped ergonomically.

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted.

This translates to savings in both money and resources.

Measuring 3,470g and 800mm in total weight and total length, respectively, this sledge hammer is available in D80mm as well as rubber insert with "Stand-Up" (art. no. 3028.281).

Product features:

- SIMPLEX sledge hammer with the insert combination of rubber composition (black, medium hard, impact cushioning, odourless, low-wear) / nylon (white, hard, very wear-resistant, no chipping even in sub-zero temperatures, oil and grease resistant).
- Cast iron housing with integrated handle protection sleeve and excellent break resistance.
- Long-fibre and ultra durable hickory handle, varnished and shaped ergonomically.
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in D80mm (total weight of 3,470g) as well as rubber insert with "Stand-Up".

Application Areas

Assembly of sharp-edged workpieces, housing assembly, plant construction, hall construction, steel construction, exhibition stand construction, repair and maintenance work

Material

Handle

- Hickory

insert 1

- Rubber composition, black
- Medium hard
- impact cushioning
- Odorless
- Low-wear

insert 2

- Nylon, white
- hard
- Very wear-resistant
- no chipping (even at temperatures below zero)
- Oil and grease resistant

Housing

- Cast iron

Order information

Ø	Dimensions		Length x Width x Height [mm]	[g]	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
80	175	800	800 x 175 x 80	3470	4030618302322	AAA938c002	21-04-09-20	3028.081

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.