Spacer Plates • for hinges EH 25160.




Product Description

Spacer plates are used for height compensation when installing hinges.

Material

 Stainless steel 1.4301, matt, vibratory ground

Drawing



Order information

Dimensions						Ť.	Art. No.
I1	b ₁	h	b ₂	d	l ₂	-	
[mm]						[g]	
30	10.8	1.0	6.0	4	18	2.2	25160.0605
30	10.8	1.5	6.0	4	18	3.3	25160.0610
30	10.8	3.0	6.0	4	18	6.5	25160.0615
30	10.8	5.0	6.0	4	18	11.0	25160.0620
40	14.5	1.0	7.5	5	25	4.3	25160.0625
40	14.5	1.5	7.5	5	25	6.4	25160.0630
40	14.5	3.0	7.5	5	25	12.0	25160.063
40	14.5	5.0	7.5	5	25	20.0	25160.064
50	18.0	1.0	10.0	6	30	6.6	25160.064
50	18.0	1.5	10.0	6	30	9.8	25160.065
50	18.0	3.0	10.0	6	30	19.0	25160.065
50	18.0	5.0	10.0	6	30	31.0	25160.066
60	21.5	1.0	12.5	8	36	9.2	25160.066
60	21.5	1.5	12.5	8	36	14.0	25160.067
60	21.5	3.0	12.5	8	36	27.0	25160.067
60	21.5	5.0	12.5	8	36	44.0	25160.0680

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.