

## SIMPLEX soft-face mallets • Plastic / nylon; with cast iron housing and high-quality wooden handle EH 3068.



### Product Description

The SIMPLEX series 3068 comes with the insert combination of plastic / nylon. The red plastic insert (series 3206) is hard and also oil and grease resistant. The nylon insert (series 3208) offers outstanding impact qualities and is guaranteed to combine maximum strength with unique durability. Composed of extruded and extremely homogeneous material, it is considerably more wear-resistant and durable and will not chip even at temperatures below zero. Made of cast iron, the housing comes with an integrated handle protection sleeve that provides for a high level of break resistance. Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt. In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources. This version is available in sizes ranging from D30mm to D60mm.

#### Product features:

- SIMPLEX soft-face mallet with the insert combination of plastic (red, hard, oil and grease resistant) / nylon (white, hard, very wear-resistant, no chipping even in sub-zero temperatures, oil and grease resistant).
- Cast iron housing with integrated handle protection sleeve and excellent break resistance.
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in sizes of D30mm to D60mm.

### Application Areas

Versatile use, assembly and repair work, maintenance work, sheet-metal forming, prefabricated house construction, carpenter's work, scaffold construction, tent construction

### Material

#### Handle

- Wood

#### insert 1

- Plastic, red
- hard
- Oil and grease resistant
- Universal

#### insert 2

- Nylon, white
- hard
- Very wear-resistant
- no chipping (even at temperatures below zero)
- Oil and grease resistant

#### Housing

- Cast iron

### Order information

| Ø  | Dimensions |     | Length x Width x Height<br>[mm] | [g]  | GTIN          | profi@ss<br>5.0 | ecl@ss 10.1 | Art. No.                 |
|----|------------|-----|---------------------------------|------|---------------|-----------------|-------------|--------------------------|
|    | —          | —   |                                 |      |               |                 |             |                          |
| 30 | 90         | 295 | 295 x 90 x 30                   | 337  | 4030618302506 | AAA905c002      | 21-04-09-16 | <a href="#">3068.030</a> |
| 40 | 115        | 325 | 325 x 115 x 40                  | 616  | 4030618302513 | AAA905c002      | 21-04-09-16 | <a href="#">3068.040</a> |
| 50 | 135        | 370 | 370 x 135 x 50                  | 1140 | 4030618302520 | AAA905c002      | 21-04-09-16 | <a href="#">3068.050</a> |
| 60 | 150        | 405 | 405 x 150 x 60                  | 1505 | 4030618304647 | AAA905c002      | 21-04-09-16 | <a href="#">3068.060</a> |

## Compliance

### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.