

## Drop-mallets • non-rebound

EH 3408.



### Product Description

Halder's 3408 series offers drop-mallets in a variety of sizes ranging from D20mm to D50mm. Drop-mallets are, in effect, soft-face mallets without a handle, allowing the user to hold the hammer head directly in the hand. Suitable for use in situations where limited accessibility makes it impossible to work with a mallet, they are also ideal for applying exactly the amount of impact force that is needed for striking the workpiece with perfect precision and for working with minimum force.

These little helpers are fitted on both ends with replaceable, noise-dampening, very wear-resistant and splinter-proof heads made of special nylon.

They are non-rebound tools thanks to their steel shot filling. The resulting effect is that the energy of the steel shot is transferred with a slight delay when the mallet's contact surface hits the workpiece. The reduced rebound lets the impact energy be absorbed with perfect efficiency, allowing for work with reduced strain on the joints and low noise.

Product features:

- Non-rebound.
- Both ends are equipped with replaceable heads made of a special nylon that is very wear-resistant and splinter-proof.
- Allow for gentle work with low noise and minimum force.
- Exact application of the impact force needed.
- Solutions for environments of limited accessibility.
- Available in sizes of D20mm to D50mm.

### Application Areas

Assembly, repair and maintenance in an environment of limited accessibility

### Material

#### Inserts

- Nylon, white
- hard
- Very wear-resistant
- no chipping (even at temperatures below zero)
- Oil and grease resistant

### Assembly

Nylon inserts replaceable

### More information


### Further products

- Drop-mallets/Punches kit, 4 pcs.

### Order information

Ø	↔	Dimensions		📦	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
		Length x Width x Height						
		[mm]						
20	150	150 x 20 x 20		215	4030618302087	AAA905c002	21-04-07-02	3408.020
30	155	155 x 30 x 30		470	4030618302100	AAA905c002	21-04-07-02	3408.030
40	160	160 x 40 x 40		785	4030618302124	AAA905c002	21-04-07-02	3408.040
50	165	165 x 50 x 50		1250	4030618302148	AAA905c002	21-04-07-02	3408.050

## Application example



## Compliance

### RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

### Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 23.01.2024.

### Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure  
<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.