

## SIMPLEX soft-face mallets • TPE-soft; with reinforced cast iron housing and fibre-glass handle EH 3701.



### Product Description

This SIMPLEX series 3701 is equipped with the blue TPE-soft insert (series 3201) on either side. This insert is the softest insert of the SIMPLEX line and offers strong impact cushioning for work requiring a light touch. Unlike conventional rubber mallets, it does not leave behind any undesired black marring.

The black, reinforced cast iron housing provides for greater stability thanks to the enlarged wall thicknesses and struts. The increase in weight ensures greater impact force.

Extremely rugged and durable, the fibre glass handle offers exceptional break resistance. It is shaped ergonomically and includes a non-slip handle. It possesses a smooth surface and is inorganic (non-sensitive to moisture).

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources.

This version is available in sizes ranging from D30mm to D80mm.

Product features:

- SIMPLEX soft-face mallet with TPE-soft inserts (blue, soft, no marring, strong impact cushioning) on both sides.
- Reinforced cast iron housing with great stability boosts impact force by adding weight.
- Exceptionally rugged and durable fibre glass handle with non-slip grip, inorganic (non-sensitive to moisture).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in sizes of D30mm to D80mm.

### Application Areas

For very delicate materials, gardening and landscaping, floor tiling, natural stone setting, furniture assembly, drywall construction, window and door construction, joiner's work

### Material

#### Handle

- Fibreglass with rubber grip

#### Inserts

- TPE-soft, blue
- Non-marring
- Soft

#### Housing

- Reinforced cast iron, black

### Order information

Ø	Dimensions		Length x Width x Height [mm]	[g]	GTIN	profiel@ss 5.0	ecl@ss 10.1	Art. No.
30	90	300	300 x 90 x 34	450	4030618303329	AAA905c002	21-04-09-16	3701.030
40	115	325	325 x 115 x 40	850	4030618303336	AAA905c002	21-04-09-16	3701.040
50	135	335	335 x 135 x 50	1190	4030618303343	AAA905c002	21-04-09-16	3701.050
60	150	410	410 x 150 x 68	1710	4030618303350	AAA905c002	21-04-09-16	3701.060
80	175	490	490 x 175 x 80	3290	4030618312338	AAA905c002	21-04-09-16	3701.080

### Compliance

#### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

#### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

#### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

#### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.