# SIMPLEX soft-face mallets • Rubber composition / soft metal; with reinforced cast iron housing and fibre-glass handle

EH 3729.





### **Product Description**

The SIMPLEX series 3729 comprises the insert combination of rubber composition / soft metal. Ultra low-wear, impact cushioning and odourless, the medium hard rubber insert (series 3202) offers a much longer service life than a conventional rubber hammer.

Made of aluminium, the silver soft metal insert (series 3209) is hard, heat-resistant and a replacement for a classic lead hammer.

The black, reinforced cast iron housing provides for greater stability thanks to the enlarged wall thicknesses and struts. The increase in weight ensures greater impact force.

Extremely rugged and durable, the fibre glass handle offers exceptional break resistance. It is shaped ergonomically and includes a non-slip handle. It possesses a smooth surface and is inorganic (non-sensitive to moisture).

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources.

This version is available in sizes ranging from D30mm to D80mm and as a sledge hammer (3729.081).

Product features:

- · SIMPLEX soft-face mallet with the insert combination of rubber composition (black, medium hard, impact cushioning, odourless, low-wear) / soft metal (silver, hard, heat-resistant).
- Reinforced cast iron housing with great stability boosts impact force by adding weight.
- · Exceptionally rugged and durable fibre glass handle with non-slip grip, inorganic (non-sensitive
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in sizes ranging from D30mm to D80mm and as a sledge hammer.

For high impact, straightening work, mould construction, plant construction, assembly, repair and maintenance work

#### **Material**

#### Handle

· Fibreglass with rubber grip

- · Rubber composition, black
- Medium hard
- impact cushioning
- Odorless
- · Low-wear

## insert 2

- · Soft metal, silver
- hard
- · Heat-resistant

## Housing

Erwin Halder KG

Reinforced cast iron, black

## **Order information**

Dimensions				I	GTIN	proficl@ss	ecl@ss 10.1	Art. No.
Ø		$\dashv$	Length x Width x Height	_		5.0		
[mm]				[g]				
30	90	300	300 x 90 x 34	485	4030618306047	AAA905c002	21-04-09-16	3729.030
40	115	325	325 x 115 x 40	945	4030618306054	AAA905c002	21-04-09-16	3729.040
50	135	335	335 x 135 x 50	1375	4030618306061	AAA905c002	21-04-09-16	3729.050
60	150	410	410 x 150 x 60	2030	4030618306078	AAA905c002	21-04-09-16	3729.060
80	175	490	490 x 175 x 80	3845	4030618306085	AAA905c002	21-04-09-16	3729.080



www.halder.com Page 1 of 2 Published on: 10.8.2024

## Compliance

## **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

## Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

### **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 2 of 2
Published on: 10.8.2024

Erwin Halder KG www.halder.com