

Charnières • corps long

25165.0020



Description produit

The different versions cover many applications that require a low load.

These metal hinges are characterised by their simple design and the different versions:

- without bores
- with bores
- with bores for countersunk screws

The version without bores can be assembled by welding or by inserting a specific drilling pattern.

Matières


Corps

- inox 1.4301

Axe

- inox 1.4301


Plan




croquis 1

croquis 2

croquis 3



Informations détaillées

b ₁	l ₁	Dimensions			Force de retenue				Référence article
		d ₂	h ₁ ~	h ₂	F ₁ ~	F ₂ ~	F ₃ ~		
		[mm]			[N]			[g]	
sans lisses – croquis 1, inox									
30	45	3	6	1,5	1300	750	700	22	25165.0020

Conformité

Conforme à la directive RoHS

Conforme à la directive 2011/65/CE et à la directive 2015/863.

Ne contient pas de substances SVHC

Pas de substances SVHC avec une teneur supérieure à 0,1% m/m – Liste SVHC [REACH] au 23.01.2024.

Ne contient pas de substances de la Proposition 65

Aucune des substances de la Proposition 65 présente.

<https://www.P65Warnings.ca.gov/>

Ne contient pas de minerais de la guerre

Ce produit ne contient pas de substances classées comme "minerais de la guerre" telles que le tantale, l'étain, l'or ou le wolfram provenant de République démocratique du Congo ou de pays frontaliers.