Mounting Pads 22590.0012



Product Description

Mounting pads can be used as foot or thrust pad. Not parallel bearing surfaces up to 15° degrees can be compensated.

Material

Ball element

· Heat-treated steel, tempered, blackened

Pad


· Heat-treated steel, blackened


More information

Notes

For the versions d_1 = M10 and M12 the lock nut conforms to DIN 934.

Drawing






Order information

	Di	mensions			ws	WS Load capacity for static load	<u></u>	Ĭ	Art. No.
d ₁	d ₂	h ₁ ~	h ₂	t	"	max.	max.		
	I	[mm]	I	I	[mm]	[kN]	[°C]	[9]	
pad and ball element – picture 1, Heat-treated steel									
M12	40	26	6	11	19	35	250	112	22590.0012



Page 1 of 2 www.halder.com Published on: 10.8.2024

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Erwin Halder KG

Does not contain Proposition 65 substances

No Proposition 65 substances included.

https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 2 of 2 Published on: 10.8.2024

www.halder.com