Mounting Pads 22590.0495





Product Description

Mounting pads can be used as foot or thrust pad. Not parallel bearing surfaces up to 15° degrees can be compensated.

Material

Ball element with bolt

· Heat-treated steel, tempered, blackened

• Steel, blackened, ISO 4032

Pad

Heat-treated steel, blackened

More information

Notes


For the versions d_1 = M10 and M12 the lock nut conforms to DIN 934.




Erwin Halder KG

Page 1 of 3 www.halder.com Published on: 10.8.2024

Drawing






Order information

Dimensions d ₁ l ₁ d ₂ l ₂ h ₁ h ₂						ws	Load capacity for static load max.	max.	Ĭ	Art. No.
							[kN]	[°C]	[g]	
pad and ball element with bolt from steel – picture 2, Heat-treated steel										
M24	100	60	91	45	9.5	36	65	250	994	22590.0495

Application example



Page 2 of 3 Published on: 10.8.2024

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Erwin Halder KG

www.halder.com Page 3 of 3 Published on: 10.8.2024