Locating Pins • with ball end 22630.0550



Product Description

Ball ended locating pins facilitate easy inserting and removing avoiding clamping inclination.


Material

• Tool steel, hardened, blackened and ground

More information

- **Further products**
- Locating Pins, DIN 6321Locating Pins, with bore hole similar to DIN 6321

Drawing







picture 1



picture 2








picture 3






Order information

Dimensions									Location hole	Ĩ	Art. No.
d₁ g6	d₂ n6	d ₃ -0.01 -0.05	d₄	I ₁	l ₂	l ₃	t	r	D ₁ H7	-	
[mm]									[mm]	[g]	
ball end round ball, not stepped – picture 3, Tool steel											
50	50	50	M6	50	50	12	12	12	50	1422	22630.0550

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.