Locating Pins • with ball end 22630.0574



Product Description

Ball ended locating pins facilitate easy inserting and removing avoiding clamping inclination.

Material


Stainless steel 1.4305, ground, surface heat-treated

More information

Further products

- Locating Pins, DIN 6321Locating Pins, with bore hole similar to DIN

Drawing





Erwin Halder KG


Page 1 of 2 www.halder.com

Published on: 10.8.2024

Order information

Dimensions									Location hole	I	Art. No.
d ₁	d ₂	d ₃	d ₄	l ₁	l ₂	l ₃	t	r	D ₁	_	
g6	n6	-0.01							H7		
		-0.05									
[mm]									[mm]	[g]	
ball end round ball, not stepped – picture 3, Stainless steel											
14	14	14	M4	17	14	3.5	8	3.5	14	34	22630.0574

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 2 of 2 Published on: 10.8.2024