Locating Pins • with ball end 22630.0670



Product Description

Ball ended locating pins facilitate easy inserting and removing avoiding clamping inclination.

Material


• Stainless steel 1.4305, ground, surface heat-treated

More information

Further products

- Locating Pins, DIN 6321Locating Pins, with bore hole similar to DIN
- Locating Pins, with bore hole similar to DIN 6321


Drawing



Order information

Dimensions										Location hole	Ĩ	Art. No.
d ₁ g6	d₂ n6	d ₃ -0.01 -0.05	d₄	I ₁	I ₂	I ₃	t	r	b	D ₁ H7	-	
[mm]										[mm]	[g]	
with ball end flattened, not stepped – picture 4, Stainless steel												
10	10	10	M3	13	10	2.5	6	2.5	2.5	10	11	22630.0670

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.