Feet • DIN 6320 with threaded shank

22640.0082



Product Description


Feet according to DIN 6320 can be used in fixture construction both as feet and as a seating element and stop.

The bearing surface has no centre.

Material

· Heat-treated steel, unhardened, blackened

Drawing






Order information

Dimensions						Tightening torque	I	Art. No.
h	d₁	b	d ₂	e	s	max.	_	
[mm]						[Nm]	[9]	
30	M8	13	0	15	12	18	35	22640 0082

Application example



www.halder.com Page 1 of 2
Published on: 10.8.2024

Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Erwin Halder KG

www.halder.com Page 2 of 2

Published on: 10.8.2024