# T-Bolts • DIN 787 23030.0150



#### **Product Description**

T-bolts when combined with DIN 6330 fixture nuts (EH 23070.) and DIN 6340 plain washers (EH 23060.) become complete clamping bolts.
These T-bolts are characterised by the rolled thread.

#### Material

· Heat-treated steel, black, forged, T-slot guidance milled

#### More information

#### **Notes**

Special types on request.


#### References

For torques and strengths please refer to appendix - Technical Data -

#### **Further products**

- · Shaft / Plain Washers, DIN 6340 heat-
- Fixture Nuts, DIN 6330 (height 1,5 d)

# Drawing



#### **Order information**


T-slot size	Dimensions						I	Art. No. <sup>1)</sup>
	d	I	а	b	е	k	_	
[mm]	[mm]						[g]	
quality 8.8								
16	M14	63	15.6	45	25	9	116	23030.0150

<sup>1)</sup> DIN standards do not include these dimensions.

# **Application example**



www.halder.com Page 1 of 2 Published on: 10.8.2024



# Compliance

# **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

#### **Does not contain SVHC substances**

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Erwin Halder KG

#### **Does not contain Proposition 65 substances**

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

# **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 2 of 2 Published on: 10.8.2024