# Clamps • DIN 6314 flat 23140.0022




## **Product Description**

This clamp (clamping claw) according to DIN 6314 is mainly used in mechanical clamping technology for clamping workpieces.

#### **Material**

· Heat-treated steel, varnished


## **Drawing**



## **Order information**

Nominal dimension	Dimensions						For screws		I	Art. No.
<b>b</b> <sub>1</sub>	ı	а	b <sub>2</sub>	b <sub>3</sub>	e <sub>1</sub>	e <sub>2</sub>			_	
[mm]	[mm]						[mm]	[in]	[9]	
22	160	30	60	22	30	60	M20, M22	3/4	1793	23140.0022

# **Application example**



Page 1 of 2 www.halder.com Published on: 10.8.2024

## Compliance

## **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

#### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

#### Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

#### **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 2 of 2
Published on: 10.8.2024