Eccentric Quick Clamps • with screw 23390.0120



Product Description

For quick and easy clamping and releasing of workpieces. When using the "adjustable" design (picture 2) the lever position can be moved.

Material

Support washer

· Thermoplastic POM, glass-fiber reinforced

· Zinc die-cast, plastic coated, black, similar to RAL 9005

Inner parts

• Steel, zinc-plated by galvanization


Screw


• Steel, zinc-plated by galvanization

Adjusting nut

Steel, zinc-plated by galvanization

Drawing





Order information


Dimensions								Stroke		Ĭ	Art. No.
ı	d ₂	h ₁ max. in clamping position	d ₃	d₄	h ₂ max.	Regulating- range h ₃ min.	b	s at 90° lever position	max.		
[mm]								[mm]	[°C]	[g]	
with screw, adjustable – picture 2, Steel											
82	М8	25	20	25	19.5	2.5	20	1	80	145	23390.0120

Erwin Halder KG

www.halder.com Page 1 of 2

Published on: 10.8.2024

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 2 of 2 Published on: 10.8.2024