Eccentric Quick Clamps • with screw 23390.0230



Product Description

For quick and easy clamping and releasing of workpieces. When using the "adjustable" design (picture 2) the lever position can be moved.

Material

Support washer

· Thermoplastic PA, glass-fiber reinforced

· Zinc die-cast, plastic coated, black, similar to RAL 9005

Inner parts

• Stainless steel 1.4305


Screw


• Stainless steel 1.4305

Adjusting nut

• Stainless steel 1.4305

Drawing






Order information

Dimensions							Stroke s		Ĭ	Art. No.
I	d ₂	h ₁ max. in clamping position	d ₃	d ₅	h ₂ max.	b	at 90° lever position	max.		
[mm]							[mm]	[°C]	[g]	
with screw – picture 1, Stainless steel										
63	M5	16	16	18.5	16.4	16	0.75	80	62	23390.0230



www.halder.com Page 1 of 2 Published on: 10.8.2024

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 2 of 2 Published on: 10.8.2024