# Eccentric Quick Clamps • with female thread 23390.0303



## **Product Description**

For quick and easy clamping and releasing of workpieces. When using the "adjustable" design (picture 2) the lever position can be moved.

#### Material

# Support washer

· Thermoplastic POM, glass-fiber reinforced

#### Lever

 Zinc die-cast, plastic coated, black, similar to RAL 9005

## Threaded part

Stainless steel 1.4305


# Inner parts

• Stainless steel 1.4305

#### Adjusting nut

Stainless steel 1.4305


## Drawing



## **Order information**

Dimensions									Stroke	ß	Ĭ	Art. No.	
I	d₁	d <sub>3</sub>	d₄	h₂ max.	Regulating- range h <sub>3</sub> min.	b	t1	t₂ min. in clamping position	s at 90° lever position	max.			
[mm]									[mm]	[°C]	[g]		
with fem	with female thread, adjustable – picture 2, Stainless steel												
63	M5	16	19	16.4	1.5	16	13	3	0.75	80	66	23390.0303	

## **Application example**



# Compliance

## **RoHS compliant**

Compliant according to Directive 2011/65/EU and Directive 2015/863.

## Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

## Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

#### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.