Eccentric Quick Clamps • with screw 23390.0320



Product Description

For quick and easy clamping and releasing of workpieces. When using the "adjustable" design (picture 2) the lever position can be moved.

Material

Support washer

Thermoplastic POM, glass-fiber reinforced

Lever

 Zinc die-cast, plastic coated, black, similar to RAL 9005

Inner parts

Stainless steel 1.4305


Screw


Stainless steel 1.4305

Adjusting nut

Stainless steel 1.4305

Drawing






Order information

Dimensions								Stroke s		Ĩ	Art. No.
I	d2	h₁ max. in clamping position	d ₃	d₄	h ₂ max.	Regulating- range h ₃ min.	b	at 90° lever position	max.		
[mm]								[mm]	[°C]	[9]	
with screw, adjustable – picture 2, Stainless steel											
82	M8	25	20	25	19.5	2.5	20	1	80	145	23390.0320

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.