Adjustable Clamping Levers • with clamping screw



Product Description

Adjustable clamping levers find versatile applications when the area of use is confined or a specific lever position is required.

Material

Lever

· Zinc die-cast, plastic coated, black, similar to RAL 9005, matt structure

Inner parts

• Steel, blackened, quality 5.8

Screw

· Steel, blackened, quality 5.8

Operation

By lifting the lever the serrations are disengaged. The lever can be positioned by the serrations. On releasing the lever, the serrations are automatically re-engaged.

More information

The screw part can be exchanged.


References

The version with ball-headed (picture 3) can be combined with the thrust piece, plastic (EH 22570.).

Further products

· Thrust Pads, plastic

Drawing



Order information

Dimensions											I	Art. No.
d ₁	d ₂	I ₁	d ₃	d ₄	h ₁	h ₂	h ₃	h₄	l ₂	l ₃		
	[mm]											
with thrust pin – picture 2, black												
14	М6	40	10	4	24.5	4	3	35	45	1.8	43	24410.2184

Erwin Halder KG

Page 1 of 2 Published on: 10.8.2024

www.halder.com

Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 2 of 2
Published on: 10.8.2024

Erwin Halder KG