Adjustable Clamping Levers • with clamping screw 24410.2461



Product Description

Adjustable clamping levers find versatile applications when the area of use is confined or a specific lever position is required.

Material

Lever

· Zinc die-cast, plastic coated, orange similar to RAL 2004, matt structure

Inner parts

• Steel, blackened, quality 5.8

Screw

· Steel, blackened, quality 5.8

Operation

By lifting the lever the serrations are disengaged. The lever can be positioned by the serrations. On releasing the lever, the serrations are automatically re-engaged.

More information

Notes

The screw part can be exchanged.


References


The version with ball-headed (picture 3) can be combined with the thrust piece, plastic (EH 22570.).


Further products

· Thrust Pads, plastic

Drawing







Order information

	Dimensions											Art. No.
d₁	d ₂	I 1	d ₃	d ₄	h ₁	h ₂	h ₃	h4	l ₂	I ₃	-	
[mm]											[g]	
with thrus	t pin – pictu	re 2, orange	;									
18	M10	32	13.5	8	31	6.5	3	45	62	3.5	136	24410.2461

Ч

Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances

Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.